## Accessory for bending tungsten probe by specific angle



- ♦ Useful for situations where the objects needs to be placed in a deep position and the standard tungsten probe cannot reach the surface under normal operation.
- ♦Place tungsten probe in position and close the cover as shown below.
- ♦ Possible to change angle by replacing another block.
- **♦**The accessory with Axis Pro can operate samplings which have never been operated.

## 《Main specification》

- Accepts tungsten probe-manufactured-by Micro Support
- $\cdot$  Size of tungsten probe : length 40mm  $\times$  outside diameter 0.6mm
- $\cdot$  Set 15° or 30° (adjustment by shim,too)
- $\cdot$  Bend position : ~3mm or ~5mm from tip
- · Capable of bending 2 tungsten probes at the same time



Place one or two tungsten probe in holder.



Set guide plate.



Close cover slowly and press lightly with finger.







Image of sampling with manipulator







It's completed.